



FW424WT

Surface encl. FW2, IP30, class I, with door and brass terminals, 4x24 modules

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rows	4
Number of section in width	2
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	96
-------------------	----

**Dimensions**

Height	791 mm
Width	571 mm
Depth	150 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Number of width units	24
-----------------------	----

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	2
--------------------------	---

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK08
Ingress Protection (IP) class	IP40
Locking type	Key lock Without lock