



ADS917D



**RCBO 1P+N 6kA 127V B-16A 30mA A Class QC&QB**

**Technical Features**

**Architecture**

Type of pole	1P+N
Curve	B
Number of poles	2

**Electric current**

Rated current	16 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	18.50 A
Rated current at -20°C	18.30 A
Rated current -15°C	18.10 A
Rated current -10°C	17.90 A
Rated current -5°C	17.70 A
Rated current at 0°C	17.40 A
Rated current 5°C	17.20 A
Rated current 10°C	17 A
Rated current 15°C	16.70 A
Rated current at 20°C	16.50 A
Rated current 25°C	16.20 A
Rated current 30°C	16 A
Rated current 35°C	15.80 A
Rated current at 40°C	15.60 A
Rated current at 50°C	15.20 A
Rated current 55°C	15 A
Rated current 60°C	14.80 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1	6 kA

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Connectivity**

Type of connection	quickconnect
--------------------	--------------

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	127 V
Rated operational voltage U <sub>e</sub>	127 - 127 V
Overvoltage category according to IEC 60947-1	3

**Power**

Total power loss under I <sub>N</sub>	5.20 W
---------------------------------------	--------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Max. Altitude	2000 m
Class of energy limitation I <sup>2</sup> t	3

---

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Connection**

Cross-section of input with screws, for flexible conductors	1.5 - 4.0 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1.5 - 4.0 mm <sup>2</sup>
Cross-section of output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of output with screws, for massive conductors	1 - 25 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.1 - 2.1 Nm
---------------------------	--------------

**Capacity**

Number of modules	2
-------------------	---

**Installation, mounting**

Type of top connection for modular devices	quickconnect
Type of bottom connection for modular devices	biconnect quickbusbar

**Dimensions**

Height	94 mm
Width	35 mm
Depth	68 mm

**Use conditions**

Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

**Sustainability**

RoHS conform	Yes
--------------	-----