



WMGSD1SB

**Grid Slave Switch Black**

**Technical Features**

**Voltage**

Operating voltage	240 - 240 V
-------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	White
Material	Urea formaldehyde

**Dimensions**

Height	60 mm
Width	24 mm
Depth	40 mm

**Architecture**

Control/operation element	Push & rotative switch
---------------------------	------------------------

**Capacity**

Number of modules	1
-------------------	---

**Texts**

Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Installation mode	Installation in surface-mounted or flush-mounted housings
Type of connection	With screw terminals
Operation and control	No Bluetooth interface

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes