

**Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 63A 40kA FTC**

**Technical Features**

**Electric current**

Rated current	63 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	76.40 A
Rated current 15°C according to IEC 60947	74.90 A
Rated current 20°C according to IEC 60947	73.30 A
Rated current 25°C according to IEC 60947	71.70 A
Rated current 30°C according to IEC 60947	70 A
Rated current at 35°C according to IEC 60947	68.30 A
Rated current at 40°C according to IEC 60947	66.60 A
Rated current 45°C according to IEC 60947	64.80 A
Rated current 50°C according to IEC 60947	63 A
Rated current 55°C according to IEC 60947	61.10 A
Rated current at 60°C according to IEC 60947	59.10 A
Rated current 65°C according to IEC 60947	57.10 A
Rated current 70°C according to IEC 60947	55 A

**Architecture**

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Power**

Total power loss under IN	21.30 W
---------------------------	---------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	4 - 4 Nm
Mounting-/Connection Position	Front

**Settings**

Thermal protection knob setting xIN	1
	1

Adjustment range short-term delayed short-circuit release	0 - 0 A
---	---------

<b>Compatibility</b>	
Suitable for DIN Rail	No
<b>Main electrical attributes</b>	
Magnetic protection trip time	0 - 0 ms
<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes