



ADC316T

**RCBO Electronic 1M 1P 6kA C-16A 30mA A Class**

**Technical Features**

**Architecture**

Type of pole	1P
Curve	C

**Electric current**

Rated current	16 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	20.20 A
Rated current at -20°C	19.80 A
Rated current -15°C	19.50 A
Rated current -10°C	19.10 A
Rated current -5°C	18.80 A
Rated current at 0°C	18.40 A
Rated current 5°C	18 A
Rated current 10°C	17.60 A
Rated current 15°C	17.20 A
Rated current at 20°C	16.80 A
Rated current 25°C	16.40 A
Rated current 30°C	16 A
Rated current 35°C	15.70 A
Rated current at 40°C	15.40 A
Rated current at 50°C	14.80 A
Rated current 55°C	14.50 A
Rated current 60°C	14.20 A
Correction factor of rating current for 2 devices placed side by side	0.95
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Voltage**

Rated insulation voltage U <sub>i</sub>	250 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	253 V
Rated operational voltage U <sub>e</sub>	240 - 240 V
Overvoltage category according to IEC 60947-1	3

**Power**

Total power loss under I <sub>N</sub>	6.50 W
---------------------------------------	--------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Max. Altitude	2000 m
Class of energy limitation I <sup>2</sup> t	3

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

---

**Capacity**

Number of modules	1
-------------------	---

---

**Dimensions**

Height	92 mm
--------	-------

Width	17.70 mm
-------	----------

Depth	70 mm
-------	-------

---

**Use conditions**

Operating temperature	-5 - 55 °C
-----------------------	------------

Storage/transport temperature	-25 - 80 °C
-------------------------------	-------------