



FV52A

Surface enclosure, VegaD IP55, 950x550x275mm, 72 modules + 2 rows to complete

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	160 A
---------------	-------

Equipment

Number of rails	3
Number of rows	5
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	72
-------------------	----

Dimensions

Height	950 mm
Width	550 mm
Depth	275 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Number of width units	24
-----------------------	----

Cover, door

Type of handle	Pivoted lever
Door/cover is transparent	No

Connection

Number of conduit inlets	4
--------------------------	---

Materials

Material	Metal Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK10
Ingress Protection (IP) class	IP55
Locking type	Special tool