



WMPS22

**10AX 2 Gang 2 Way & Intermediate Wall Switch**

**Technical Features**

**Electric current**

Switching current 10 A

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 2

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 12 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Double rocker

**Electric current**

Rated current 10 A

**Texts**

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes