



TRE600



LED floodlight with PIR 220/360° RF QL white

Technical Features

Dimensions

Installation height	2.5 - 4.0 m
Recommended installation height	2.5 - 4.0 m

Settings

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

Minimal duty cycle	30 s
--------------------	------

Functions

Maximal duty cycle	15 min
--------------------	--------

Connectivity

With bus system KNX radio	Yes
---------------------------	-----

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Detection

Detection angle adjustable	45 - 90 °
Detection angle	360 - 360
Detection angle horizontal	360 - 360

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Materials

Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC)
----------	---

Texts

Function	Switch-off pre-warning on dimmer inserts Easy additional functions: +6 scenes, on/off operating mode, scene call-up upon motion/no motion With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours Reset function (to factory setting)
Installation mode	For wall mounting Plug & play connection

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes