



WMPS22

### 10AX 2 Gang 2 Way & Intermediate Wall Switch

#### Technical Features

##### Electric current

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

|                |        |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

|          |                   |
|----------|-------------------|
| Material | Urea formaldehyde |
|----------|-------------------|

|           |           |
|-----------|-----------|
| Treatment | Untreated |
|-----------|-----------|

#### Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

#### Dimensions

|            |            |
|------------|------------|
| Dimensions | 86 x 86 mm |
|------------|------------|

|                |       |
|----------------|-------|
| Built-in depth | 12 mm |
|----------------|-------|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Double rocker |
|---------------------------|---------------|

#### Electric current

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

#### Texts

|                   |  |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
|-------------------|--|

|          |  |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

|             |                           |
|-------------|---------------------------|
| Switch mode | 2-way, with loop terminal |
|-------------|---------------------------|

#### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|