



HHA018Z

Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 20A 25kA CTC

Technical Features

Electric current

Rated current I _N	20 A
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	25 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	20 kA
Rated current at 10°C according to IEC 60947	25.40 A
Rated current at 15°C according to IEC 60947	24.80 A
Rated current at 20°C according to IEC 60947	24.20 A
Rated current at 25°C according to IEC 60947	23.50 A
Rated current at 30°C according to IEC 60947	22.80 A
Rated current at 35°C according to IEC 60947	22.20 A
Rated current at 40°C according to IEC 60947	21.40 A
Rated current at 45°C according to IEC 60947	20.70 A
Rated current at 50°C according to IEC 60947	20 A
Rated current at 55°C according to IEC 60947	19.20 A
Rated current at 60°C according to IEC 60947	18.30 A
Rated current at 65°C according to IEC 60947	17.50 A
Rated current at 70°C according to IEC 60947	16.60 A

Architecture

Number of poles	1
Neutral position	Without neutral

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	690 V
Rated operational voltage U _e	220 - 240 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Power dissipation at I _N	2.70 W
-------------------------------------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	6 - 70 mm ²
Cross-section rigid conductor	6 - 95 mm ²

Installation, mounting

Nominal tightening torque	6 - 6 Nm
---------------------------	----------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Settings

Thermal protection knob setting xI _N	1
	1

Dimensions

Height	130 mm
Width	25 mm
Depth	68 mm

Cable

Cable material	Copper
----------------	--------

Compatibility

Suitable for DIN Rail	No
-----------------------	----

Installation, mounting

Nominal tightening torque down terminal	6 - 6 Nm
Nominal tightening torque top terminal	6 - 6 Nm

Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes