



HHA018Z

### Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 20A 25kA CTC

#### Technical Features

##### Electric current

|                                                                               |         |
|-------------------------------------------------------------------------------|---------|
| Rated current                                                                 | 20 A    |
| Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2 | 25 kA   |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2   | 20 kA   |
| Rated current 10°C according to IEC 60947                                     | 25.40 A |
| Rated current 15°C according to IEC 60947                                     | 24.80 A |
| Rated current 20°C according to IEC 60947                                     | 24.20 A |
| Rated current 25°C according to IEC 60947                                     | 23.50 A |
| Rated current 30°C according to IEC 60947                                     | 22.80 A |
| Rated current at 35°C according to IEC 60947                                  | 22.20 A |
| Rated current at 40°C according to IEC 60947                                  | 21.40 A |
| Rated current 45°C according to IEC 60947                                     | 20.70 A |
| Rated current 50°C according to IEC 60947                                     | 20 A    |
| Rated current 55°C according to IEC 60947                                     | 19.20 A |
| Rated current at 60°C according to IEC 60947                                  | 18.30 A |
| Rated current 65°C according to IEC 60947                                     | 17.50 A |
| Rated current 70°C according to IEC 60947                                     | 16.60 A |

##### Architecture

|                           |                 |
|---------------------------|-----------------|
| Number of poles           | 1               |
| Control/operation element | Toggle          |
| Device construction type  | Fixed built-in  |
| Neutral position          | Without neutral |

##### Tripping

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Voltage

|                                      |             |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 8000 V      |
| Rated insulation voltage Ui          | 690 V       |
| Rated operational voltage Ue         | 220 - 240 V |

##### Functions

|           |        |
|-----------|--------|
| Trip unit | TM F/F |
|-----------|--------|

##### Power

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 2.70 W |
|---------------------------|--------|

##### Endurance

|                                        |       |
|----------------------------------------|-------|
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations        | 20000 |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

##### Connection

|                                  |                        |
|----------------------------------|------------------------|
| Cross-section flexible conductor | 6 - 70 mm <sup>2</sup> |
| Cross-section rigid conductor    | 6 - 95 mm <sup>2</sup> |

##### Installation, mounting

|                               |          |
|-------------------------------|----------|
| Nominal tightening torque     | 6 - 6 Nm |
| Mounting-/Connection Position | Front    |

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

---

**Cover, door**

|               |     |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

**Settings**

|                                     |   |
|-------------------------------------|---|
| Thermal protection knob setting xIN | 1 |
|                                     | 1 |

**Cable**

|                |        |
|----------------|--------|
| Cable material | Copper |
|----------------|--------|

**Dimensions**

|        |        |
|--------|--------|
| Height | 130 mm |
| Width  | 25 mm  |
| Depth  | 68 mm  |

**Compatibility**

|                       |     |
|-----------------------|-----|
| Suitable for DIN Rail | Yes |
|-----------------------|-----|

**Installation, mounting**

|                                         |          |
|-----------------------------------------|----------|
| Nominal tightening torque down terminal | 6 - 6 Nm |
| Nominal tightening torque top terminal  | 6 - 6 Nm |

**Main electrical attributes**

|                               |          |
|-------------------------------|----------|
| Magnetic protection trip time | 0 - 0 ms |
|-------------------------------|----------|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|