



LNH1160M

HRC LV fuse NH1 gG AC500V 160A double indicator with live gripping-lugs

Technical Features

Architecture

|       |    |
|-------|----|
| Curve | gG |
|-------|----|

Fuse

|           |     |
|-----------|-----|
| Fuse size | NH1 |
|-----------|-----|

|                      |    |
|----------------------|----|
| Fuse characteristics | gG |
|----------------------|----|

Voltage

|                     |       |
|---------------------|-------|
| Type voltage supply | AC/DC |
|---------------------|-------|

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 500 - 500 V |
|------------------------------|-------------|

|                           |             |
|---------------------------|-------------|
| Rated voltage at AC 50 Hz | 500 - 500 V |
|---------------------------|-------------|

Electric current

|               |       |
|---------------|-------|
| Rated current | 160 A |
|---------------|-------|

Use conditions

|           |    |
|-----------|----|
| Insulated | No |
|-----------|----|

Main electrical attributes

|   |        |
|---|--------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 120 kA |
|---|--------|

Power

|                           |         |
|---------------------------|---------|
| Total power loss under IN | 14.60 W |
|---------------------------|---------|

Dimensions

|        |          |
|--------|----------|
| Height | 64.50 mm |
|--------|----------|

|       |        |
|-------|--------|
| Width | 135 mm |
|-------|--------|

|       |        |
|-------|--------|
| Depth | 135 mm |
|-------|--------|

Sustainability

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|