

**Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 160A 25kA FTC**

**Technical Features**

**Electric current**

|                                                                                           |          |
|-------------------------------------------------------------------------------------------|----------|
| Rated current                                                                             | 160 A    |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2 | 25 kA    |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2 | 35 kA    |
| Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2   | 25 kA    |
| Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2   | 20 kA    |
| Rated current 10°C according to IEC 60947                                                 | 187.20 A |
| Rated current 15°C according to IEC 60947                                                 | 184 A    |
| Rated current 20°C according to IEC 60947                                                 | 180.70 A |
| Rated current 25°C according to IEC 60947                                                 | 177.40 A |
| Rated current 30°C according to IEC 60947                                                 | 174.10 A |
| Rated current at 35°C according to IEC 60947                                              | 170.70 A |
| Rated current at 40°C according to IEC 60947                                              | 167.20 A |
| Rated current 45°C according to IEC 60947                                                 | 163.60 A |
| Rated current 50°C according to IEC 60947                                                 | 160 A    |
| Rated current 55°C according to IEC 60947                                                 | 156.20 A |
| Rated current at 60°C according to IEC 60947                                              | 152.40 A |
| Rated current 65°C according to IEC 60947                                                 | 148.50 A |
| Rated current 70°C according to IEC 60947                                                 | 144.40 A |

**Architecture**

|                 |   |
|-----------------|---|
| Number of poles | 4 |
|-----------------|---|

**Tripping**

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Voltage**

|                                                  |        |
|--------------------------------------------------|--------|
| Rated impulse withstand voltage U <sub>imp</sub> | 8000 V |
| Rated insulation voltage U <sub>i</sub>          | 690 V  |

**Functions**

|           |        |
|-----------|--------|
| Trip unit | TM F/F |
|-----------|--------|

**Power**

|                                       |         |
|---------------------------------------|---------|
| Total power loss under I <sub>N</sub> | 43.80 W |
|---------------------------------------|---------|

**Endurance**

|                                        |       |
|----------------------------------------|-------|
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations        | 20000 |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

**Connection**

|                                  |                        |
|----------------------------------|------------------------|
| Cross-section flexible conductor | 4 - 70 mm <sup>2</sup> |
| Cross-section rigid conductor    | 4 - 95 mm <sup>2</sup> |

**Settings**

|                                                 |   |
|-------------------------------------------------|---|
| Thermal protection knob setting xI <sub>N</sub> | 1 |
|                                                 | 1 |

**Dimensions**

|        |        |
|--------|--------|
| Height | 130 mm |
| Width  | 100 mm |
| Depth  | 68 mm  |

Product Datasheet

HHA161P

---

|                                   |          |
|-----------------------------------|----------|
| <b>Compatibility</b>              |          |
| Suitable for DIN Rail             | No       |
| <b>Main electrical attributes</b> |          |
| Magnetic protection trip time     | 0 - 0 ms |
| <b>Sustainability</b>             |          |
| REACH-SVHC free                   | Yes      |
| RoHS conform                      | Yes      |