



WGMS213S

## 13A TWIN SWITCHED SOCKET

### Technical Features

#### Voltage

Rated voltage	250 V
---------------	-------

#### Electric current

Output current	0 mA
Rated current	13 A

#### Voltage

Output voltage	0-0 V
----------------	-------

#### Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Output power	0 W
Power consumption standby	0 W

#### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

#### Dimensions

Height	18 mm
Width	86 mm
Depth	18 mm

#### Cable

Cable length	0 m
--------------	-----

#### Dimensions

Built-in depth flush-mounted boxes	35 mm
Built-in depth	18 mm

#### Connection

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0,08 - 4 mm <sup>2</sup>

#### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Back

#### Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No

#### Accessories

Has labelling field	No
Pre-equipped with	None

---

**Capacity**

---

Number of modules	0
-------------------	---

---

**Safety**

---

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

---

**Functions**

---

With orientation lighting	No
With function lighting	No

---

**Identification**

---

With imprint	No
--------------	----

---

**Sustainability**

---

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

---