



WBQSA3-MB

### FIN Architrave 3 gang MB

#### Technical Features

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

#### Materials

|        |       |
|--------|-------|
| Colour | Black |
|--------|-------|

#### Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP2X |
|-------------------------------|------|

#### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

#### Texts

|                   |                     |
|-------------------|---------------------|
| Installation mode | For screw fastening |
|-------------------|---------------------|

|                    |                      |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

|          |  |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

|             |                           |
|-------------|---------------------------|
| Switch mode | 2-way, with loop terminal |
|-------------|---------------------------|

#### Sustainability

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|