



HI462

**Change-over switch 4P 1250A**

**Technical Features**

**Voltage**

Rated insulation voltage $U_i$	1000 V
Rated impulse withstand voltage $U_{imp}$	12000 V

**Electric current**

Rated current	1250 A
Rated short-time withstand current $I_{cw}$ IEC 60947	64 kA
Rated conditional short-circuit current $I_{cc}$ with gl-gG fuses	100 kA

**Power**

Rated operational power under 400 V AC AC1	822000 W
--------------------------------------------	----------

**Architecture**

Number of poles	4
Control/operation element	Long rotary handle
Type of pole	4P

**Dimensions**

Height	330 mm
Width	466 mm
Depth	375 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Cover, door**

Interlockable	Yes
---------------	-----

**Safety**

Ingress Protection (IP) class	IP00
-------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Total power loss under IN	373.20 W
---------------------------	----------

**Use conditions**

Operating temperature	-20 - 70 °C
-----------------------	-------------

**Connection**

Cross-section rigid conductor	4x 185 mm <sup>2</sup>
-------------------------------	------------------------