



HDA014Z

Moulded Case Circuit Breaker X160 1P 18kA 16A

Technical Features

Electric current

Rated current	16 A
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	22 A
Rated current 15°C according to IEC 60947	21.30 A
Rated current 20°C according to IEC 60947	20.60 A
Rated current 25°C according to IEC 60947	19.90 A
Rated current 30°C according to IEC 60947	19.20 A
Rated current at 35°C according to IEC 60947	18.40 A
Rated current at 40°C according to IEC 60947	17.60 A
Rated current 45°C according to IEC 60947	16.80 A
Rated current 50°C according to IEC 60947	16 A
Rated current 55°C according to IEC 60947	15 A
Rated current at 60°C according to IEC 60947	14.10 A
Rated current 65°C according to IEC 60947	13 A
Rated current 70°C according to IEC 60947	11.90 A

Architecture

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	690 V
Rated operational voltage U _e	220 - 240 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Total power loss under I _N	1.80 W
---------------------------------------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	4 - 70 mm ²
Cross-section rigid conductor	4 - 95 mm ²

Installation, mounting

Nominal tightening torque	6 - 6 Nm
Mounting-/Connection Position	Front

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Settings

Thermal protection knob setting xIN	1
	1
Adjustment range short-term delayed short-circuit release	0 - 0 A

Compatibility

Suitable for DIN Rail	No
-----------------------	----

Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------