



WBQSV3-MW

FIN 3 Gang Switch Plate cw mechs MW

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	3
-------------------	---

Dimensions

Dimensions	117 x 77.00 mm
Built-in depth	23 mm
Built-in depth flush-mounted boxes	23 mm

Safety

Ingress Protection (IP) class	IP2X
Impact resistance IK	IK08

Electric current

Rated current	16 A
---------------	------

Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way, with loop terminal

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes