



ESL226

Contactor 25A, 2NC, 12V~50Hz

Technical Features

Connection

Type of contacts	2NC
------------------	-----

Electric current

Rated current	25 A
---------------	------

Capacity

Number of modules	1
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Rated insulation voltage Ui	250 V
-----------------------------	-------

Rated operational voltage Ue	230 - 230 V
------------------------------	-------------

Command voltage AC	12 - 12 V
--------------------	-----------

Command voltage DC	0 - 0 V
--------------------	---------

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Use

Category of use	AC-7a/AC-7b
-----------------	-------------

Use conditions

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

Endurance

Number of mechanical operations	1000000
---------------------------------	---------

Electric endurance in number of cycles	30000
--	-------

Power

Total power loss under IN	3 W
---------------------------	-----

Inrush power absorbed	10.70 VA
-----------------------	----------

Dimensions

Height	83 mm
--------	-------

Width	17.85 mm
-------	----------

Depth	60 mm
-------	-------

Connection

Number of contacts	2
--------------------	---

Equipment

Number of NO contacts	0
-----------------------	---

Number of NC contacts	2
-----------------------	---

With switch for manual switch	No
-------------------------------	----

Connection

Cross-section flexible conductor	1 - 6 mm ²
----------------------------------	-----------------------

Cross-section rigid conductor	1 - 10 mm ²
-------------------------------	------------------------

Installation, mounting

Nominal tightening torque	1.20 - 1.20 Nm
---------------------------	----------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----