



HI456

**Change-over switch 4P 400A**

**Technical Features**

**Voltage**

Rated insulation voltage $U_i$	1000 V
Rated impulse withstand voltage $U_{imp}$	12000 V

**Electric current**

Rated current	400 A
Rated short-time withstand current $I_{cw}$ IEC 60947	15 kA
Rated conditional short-circuit current $I_{cc}$ with gI-gG fuses	50 kA

**Power**

Rated operational power under 400 V AC AC1	263000 W
--	----------

**Architecture**

Number of poles	4
Control/operation element	Long rotary handle
Type of pole	4P

**Dimensions**

Height	170 mm
Width	312 mm
Depth	218 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Cover, door**

Interlockable	Yes
---------------	-----

**Safety**

Ingress Protection (IP) class	IP00
-------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Capacity**

Number of modules	12
-------------------	----

**Power**

Total power loss under $I_N$	60.40 W
------------------------------	---------

**Connection**

Cross-section rigid conductor	185 - 240 mm <sup>2</sup>
-------------------------------	---------------------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes