



JK1B084F2

125A TPN BOARD,INVICTA,8+4WAY,FLUSH,FOR 50 OC TESTING

Technical Features

Connection

Number of accessible phases	3
-----------------------------	---

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Breaking and opening capacity Idm	0 kA
-----------------------------------	------

Equipment

Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis

Capacity

Number of modules	0
-------------------	---

Dimensions

Height	800 mm
Width	470 mm
Depth	5 mm

Cover, door

Number of cabinet doors	1
Door/cover is transparent	No

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP41
Locking type	Special tool Without lock

Architecture

Number of poles	24
-----------------	----

Sustainability

REACH-SVHC free	Yes
-----------------	-----