



TYB708D



Universal interface 8gang comfort

Technical Features

Settings

Supported configuration mode	ETS
------------------------------	-----

Electric current

Number of entry circuits	8
--------------------------	---

Equipment

External signal voltage necessary	Yes
-----------------------------------	-----

Connectivity

With bus system KNX radio	No
---------------------------	----

Equipment

Radio frequency bidirectional	No
-------------------------------	----

With battery	No
--------------	----

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Lighting

LED controlling	Yes
-----------------	-----

Materials

Colour	Black
--------	-------

RAL code	9005
----------	------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Cable

Cable length	10 m
--------------	------

Voltage

Input voltage	20 - 20 V
---------------	-----------

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Type voltage supply	DC
---------------------	----

System supply voltage	30 V DC Via bus
-----------------------	-----------------

Dimensions

Depth	32 mm
-------	-------

Texts

Type of connection	With screw terminals
--------------------	----------------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----