



LFS6010009016

Trunking LFS made of steel 60x100mm in traffic white

Technical Features

Dimensions

Height	60 mm
Width	100 mm
Length	2000 mm
Inner cross-section	5025 - 5025 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	21
--	----

Materials

Material	Steel
Treatment	Varnished
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP30

Standards

Suitable for functional integrity according to DIN4102-12	Yes
---	-----

Use conditions

Operating temperature	-5 - 90 °C
-----------------------	------------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Equipment

Number of partitions	0
Number of compartments	1 - 2
Number of pluggable partitions	1
Cable retaining clip included	Yes
With protective film	No

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

