



HDS061EC

Moulded Case Circuit Breaker h3+ P160 TM FIX 1P1D 63A 18kA CTC

Technical Features

Electric current

Rated current	63 A
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	76.80 A
Rated current 15°C according to IEC 60947	75.20 A
Rated current 20°C according to IEC 60947	73.60 A
Rated current 25°C according to IEC 60947	71.90 A
Rated current 30°C according to IEC 60947	70.20 A
Rated current at 35°C according to IEC 60947	68.50 A
Rated current at 40°C according to IEC 60947	66.70 A
Rated current 45°C according to IEC 60947	64.80 A
Rated current 50°C according to IEC 60947	63 A
Rated current 55°C according to IEC 60947	61 A
Rated current at 60°C according to IEC 60947	59 A
Rated current 65°C according to IEC 60947	56.90 A
Rated current 70°C according to IEC 60947	54.70 A

Architecture

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	800 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Total power loss under I _N	5.10 W
---------------------------------------	--------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Installation, mounting

Mounting-/Connection Position	Front
-------------------------------	-------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Cover, door

Interlockable	No
---------------	----

Settings

Thermal protection knob setting xI _N	1
	1

Dimensions

Height	130 mm
Width	30 mm
Depth	68 mm

Compatibility

Compatible with RDC AOB	No
Suitable for DIN Rail	No

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes