



FW436WT

Surface encl. FW2, IP30, class I, with door and brass terminals, 4x36 modules

#### Technical Features

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	125 A
---------------	-------

##### Equipment

Number of rows	4
Number of section in width	3
With lock	No
Has neutral terminal block	No

##### Capacity

Number of modules	144
-------------------	-----

##### Dimensions

Height	791 mm
Width	787 mm
Depth	150 mm

##### Cover, door

Number of cabinet doors	1
-------------------------	---

##### Dimensions

Number of width units	36
-----------------------	----

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Connection

Number of conduit inlets	3
--------------------------	---

##### Materials

Material	Steel
RAL code	9010
Colour	Pure white

##### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

##### Safety

Protection class	Isolation class I
Impact resistance IK	IK08
Ingress Protection (IP) class	IP30
Locking type	Key lock Without lock