



WBQSV5-MW

FIN 5 Gang Switch Plate cw mechs MW

Technical Features

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 5 |
|-------------------|---|

Dimensions

| | |
|------------|-------------|
| Dimensions | 117 x 77 mm |
|------------|-------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP2X |
|-------------------------------|------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Texts

| | |
|--------------------|--|
| Installation mode | For screw fastening |
| Type of connection | With screw terminals |
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-way, with loop terminal |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |