



WNA001B

IP55

cubyko 2-way switch composable white IP55

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting
Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white
RAL code 9010
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Identification

Assembly arrangement Control element

Connectivity

Mounting type Screw mounting
With claw mounting No

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 70 x 70 mm
Built-in depth 12 mm
Built-in depth flush-mounted boxes 0 mm
Height of P-touch band for labelling field 12 mm

Safety

Ingress Protection (IP) class IP55
Impact resistance IK IK08

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Connection

Type of contacts 2-way
Connector/plug type Turn screw lock

Texts

Installation mode For screw fastening
Type of connection With plug-in terminals
Switch mode Change-over

Sustainability

Halogen free Yes
REACH-SVHC free Yes
RoHS conform Yes