



JK1E32F

125A TPN Extension box, invicta, 32 Module with Din Rail, depth120mmm, flush

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|-----------------------------------|------|
| Breaking and opening capacity Idm | 0 kA |
|-----------------------------------|------|

Equipment

| | |
|------------------------|------------|
| Number of rows | 2 |
| Has mounting plate | No |
| Equipped with switch | No switch |
| Number of switches | 0 |
| Type of busbar chassis | No chassis |

Capacity

| | |
|-------------------|----|
| Number of modules | 10 |
|-------------------|----|

Dimensions

| | |
|-----------------------|--------|
| Height | 450 mm |
| Width | 430 mm |
| Depth | 5 mm |
| Number of width units | 16 |

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 1 |
| Door/cover is transparent | No |

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9002 |
| Colour | Grey white |

Safety

| | |
|-------------------------------|------------------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP41 |
| Locking type | Special tool Without lock |

Architecture

| | |
|-----------------|----|
| Number of poles | 32 |
|-----------------|----|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |