



BD226

Earth leakage add-on block 2P 63A 500mA AC S Class

Technical Features

Voltage

| | |
|--------------------------------------|-------------|
| Rated operational voltage Ue | 230 - 400 V |
| Rated insulation voltage Ui | 500 V |
| Rated impulse withstand voltage Uimp | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Electric current

| | |
|--------------------------------------|--------|
| Rated residual operating current Idn | 500 mA |
| Rated current | 63 A |

Architecture

| | |
|------------------|------|
| Number of poles | 2 |
| Neutral position | Left |

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Connectivity

| | |
|---|------------------|
| Down connection alignment for modular devices | Aligned terminal |
|---|------------------|

Dimensions

| | |
|--------|-------|
| Height | 70 mm |
| Width | 35 mm |
| Depth | 92 mm |