



HIC406A

Motorized changeover switch 4P 63A 400V

Technical Features

Voltage

|                                          |             |
|------------------------------------------|-------------|
| Rated operational voltage U <sub>e</sub> | 380 - 415 V |
|------------------------------------------|-------------|

Electric current

|                                                                          |       |
|--------------------------------------------------------------------------|-------|
| Rated current                                                            | 63 A  |
| Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses | 50 kA |

Power

|                                            |         |
|--------------------------------------------|---------|
| Rated operational power under 400 V AC AC1 | 41000 W |
|--------------------------------------------|---------|

Architecture

|                          |                |
|--------------------------|----------------|
| Number of poles          | 4              |
| Device construction type | Fixed built-in |

Compatibility

|                                 |     |
|---------------------------------|-----|
| Suitable for DIN Rail           | Yes |
| Suitable for distribution board | Yes |

Installation, mounting

|             |                            |
|-------------|----------------------------|
| Mounting on | DIN rail<br>Mounting plate |
|-------------|----------------------------|

Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |