Product Datasheet
MW110

MW110

MCB 1P 3kA C-10A 1M

Technical Features

Electric current	
Rated current	10 A
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	3 kA
Architecture	
Type of pole	1P
Curve	C
Capacity	
Number of modules	1
Main electrical attributes	
Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	3 kA
Installation, mounting	
Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm
Voltage	
Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V
Frequency	
Frequency	50 - 60 Hz
Connection	
Cross-section of input and output with screws, for massive conductors	1 - 35 mm^2
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm^2
Cross-section of input with screws, for flexible conductors	1 - 25 mm^2
Cross-section of input with screws, for massive conductors	1 - 35 mm^2
Installation, mounting	
Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes
Safety	
Ingress Protection (IP) class	IP20
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I^2t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C
Power	
Total power loss under IN	1.63 W
Connectivity	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
Dimensions	
Height	83 mm
Width	17.50 mm
Depth	70 mm

Sustainability	
RoHS conform	Yes