



WXF054

Automatic switch gallery slave and staircase

Technical Features

Detection

Detection angle	180 - 180
Type of sensor	Movement detector
Detection angle horizontal	90 - 180

Settings

Minimal duty cycle	0.20 s
Response brightness adjustable	Yes
Response sensitivity adjustable	Yes

Lighting

Photocell sensitivity	5 - 1000 lx
-----------------------	-------------

Settings

Switch off delay time	0 s
Switch on delay time	0 s

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Width	45 mm
Built-in depth	28.20 mm
Installation height	1.10 - 1.10 m

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Colour	Light grey
Material	Polycarbonate (PC)
Surface finish	Matt

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Mounting on	Flush mounting
Ceiling mounting possible	No

Electric current

Control current	1.30 - 1.30 mA
-----------------	----------------

Reach distance

Max. transmission range frontally	12 m
Max. transmission range sideways	8 m