



SPA001N

**Cartridge N-PE Uc 350V Iimp 100kA Up 1.5kV**

**Technical Features**

**Electric current**

Max. discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	100 kA
---------------------------------------------------	--------

**Network configuration**

Network type	TN TT
--------------	----------

**Connectivity**

Type of connection	Plug-in connection
--------------------	--------------------

**Electric current**

Lightning impulse current Iimp (10/350 μs) IEC 61643 L-N(PEN)/ N-PE	100 kA
---------------------------------------------------------------------	--------

**Equipment**

With remote signalling contact	No
--------------------------------	----

**Capacity**

Number of modules	2
-------------------	---

**Voltage**

Voltage protection level Up according to IEC 61643-1	1.50 kV
Continuous operating voltage Uc according to IEC 61643-1	350 V
Rated operational voltage Ue	240 - 240 V

**Architecture**

Number of poles	1
-----------------	---

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Dimensions**

Height	46.40 mm
Width	35.50 mm
Depth	59.4 mm

**Controls and indicators**

With indicator lamp	Yes
---------------------	-----

**Standards**

Requirement class IEC 61643	T1 T2
-----------------------------	----------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Sustainability**

RoHS conform	Yes
--------------	-----