



TRB201



Module 1 output 16A flush mounted KNX

Technical Features

Connectivity

|                |           |
|----------------|-----------|
| Radio protocol | KNX Radio |
|----------------|-----------|

Settings

|                              |                          |
|------------------------------|--------------------------|
| Supported configuration mode | ETS<br>easy<br>quicklink |
|------------------------------|--------------------------|

Connectivity

|                           |     |
|---------------------------|-----|
| Receiver category         | 2   |
| With bus system KNX       | No  |
| With bus system KNX radio | Yes |

Dimensions

|                |       |
|----------------|-------|
| Height         | 30 mm |
| Built-in depth | 35 mm |

Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Materials

|        |            |
|--------|------------|
| Colour | Light grey |
|--------|------------|

Equipment

|                               |     |
|-------------------------------|-----|
| Radio frequency bidirectional | Yes |
| With switch for manual switch | No  |

Electric current

|                   |      |
|-------------------|------|
| Switching current | 16 A |
|-------------------|------|

Frequency

|                           |                     |
|---------------------------|---------------------|
| Frequency                 | 50 - 60 Hz          |
| Radio reception frequency | 868.30 - 868.30 MHz |

Power

|                                     |        |
|-------------------------------------|--------|
| Output power                        | 3680 W |
| 230 V incandescent and halogen lamp | 2300 W |

Voltage

|                                          |             |
|------------------------------------------|-------------|
| Operating voltage                        | 230 - 230 V |
| Rated operational voltage U <sub>e</sub> | 230 - 230 V |
| System supply voltage                    | 230 V AC    |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | 0 - 45 °C |
|-----------------------|-----------|

Connection

|                                  |                     |
|----------------------------------|---------------------|
| Cross-section rigid conductor    | 2.5 mm <sup>2</sup> |
| Cross-section flexible conductor | 2.5 mm <sup>2</sup> |

Texts

|                    |                                                                                                |
|--------------------|------------------------------------------------------------------------------------------------|
| Function           | Easy additional functions: +6 scenes, repeater function<br>Reset function (to factory setting) |
| Installation mode  | For installation behind flush-mounted inserts                                                  |
| Type of connection | With screw-in lift terminals                                                                   |

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|