



MY340E

### MCB 3P 4.5kA C-40A 3M

#### Technical Features

##### Electric current

|                                                                                               |         |
|-----------------------------------------------------------------------------------------------|---------|
| Rated current I <sub>N</sub>                                                                  | 40 A    |
| Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1 | 6 kA    |
| Rated current at -15°C                                                                        | 48,8 A  |
| Rated current at -10°C                                                                        | 47,82 A |
| Rated current at -5°C                                                                         | 46,84 A |
| Rated current at 0°C                                                                          | 45,86 A |
| Rated current at 5°C                                                                          | 44,89 A |
| Rated current at 10°C                                                                         | 43,91 A |
| Rated current at 15°C                                                                         | 42,93 A |
| Rated current at 20°C                                                                         | 41,95 A |
| Rated current at 25°C                                                                         | 40,98 A |
| Rated current at 30°C                                                                         | 40 A    |
| Rated current at 35°C                                                                         | 38,86 A |
| Rated current at 40°C                                                                         | 37,72 A |
| Rated current at 45°C                                                                         | 36,59 A |
| Rated current at 50°C                                                                         | 35,45 A |
| Rated current at 55°C                                                                         | 34,31 A |
| Rated current at 60°C                                                                         | 33,17 A |
| Rated current at 65°C                                                                         | 32,04 A |
| Rated current at 70°C                                                                         | 30,9 A  |
| Rated short-circuit breaking capacity I <sub>cn</sub> under 400 V AC according to IEC 60898-1 | 4,5 kA  |

##### Architecture

|              |    |
|--------------|----|
| Type of pole | 3P |
| Curve        | C  |

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

##### Main electrical attributes

|                                                                                   |        |
|-----------------------------------------------------------------------------------|--------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 4,5 kA |
|-----------------------------------------------------------------------------------|--------|

##### Installation, mounting

|                                         |                |
|-----------------------------------------|----------------|
| Nominal tightening torque top terminal  | 2,80 - 2,80 Nm |
| Nominal tightening torque down terminal | 2,80 - 2,80 Nm |

##### Voltage

|                                                  |             |
|--------------------------------------------------|-------------|
| Rated operational voltage U <sub>e</sub>         | 400 - 400 V |
| Type voltage supply                              | AC          |
| Rated insulation voltage U <sub>i</sub>          | 500 V       |
| Rated impulse withstand voltage U <sub>imp</sub> | 4000 V      |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Connection

|                                                                        |                        |
|------------------------------------------------------------------------|------------------------|
| Cross-section of input and output with screws, for massive conductors  | 1 - 35 mm <sup>2</sup> |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for flexible conductors            | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for massive conductors             | 1 - 35 mm <sup>2</sup> |
| Cross-section flexible conductor                                       | 1 - 25 mm <sup>2</sup> |
| Cross-section rigid conductor                                          | 1 - 35 mm <sup>2</sup> |

##### Installation, mounting

|                                               |                |
|-----------------------------------------------|----------------|
| Nominal tightening torque                     | 2,80 - 2,80 Nm |
| Type of bottom connection for modular devices | biconnect      |
| Type of top connection for modular devices    | Screw terminal |
| 360° mounting position possible               | Yes            |

---

**Safety**

|                               |       |
|-------------------------------|-------|
| Ingress Protection (IP) class | IP20  |
| Grid distance                 | 35 mm |

**Use conditions**

|                                                          |                  |
|----------------------------------------------------------|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2                |
| Class of energy limitation I <sup>2</sup> t              | 3                |
| Air humidity protection                                  | For all climates |
| Operating temperature                                    | -25 - 70 °C      |

**Power**

|                         |         |
|-------------------------|---------|
| Power dissipation at IN | 18,70 W |
|-------------------------|---------|

**Connectivity**

|                                               |                  |
|-----------------------------------------------|------------------|
| Top connection alignment for modular devices  | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |
| Type of connection                            | Screw terminal   |

**Dimensions**

|        |          |
|--------|----------|
| Height | 83 mm    |
| Width  | 52,50 mm |
| Depth  | 70 mm    |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |