



NDN106A

**MCB 1P 10kA/15kA D-6A 1M**

**Technical Features**

**Electric current**

Rated current	6 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	7.50 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	15 kA
Rated current -25°C	7.51 A
Rated current at -20°C	7.39 A
Rated current -15°C	7.26 A
Rated current -10°C	7.13 A
Rated current -5°C	7 A
Rated current at 0°C	6.87 A
Rated current 5°C	6.73 A
Rated current 10°C	6.59 A
Rated current 15°C	6.45 A
Rated current at 20°C	6.30 A
Rated current 25°C	6.15 A
Rated current 30°C	6 A
Rated current 35°C	5.84 A
Rated current at 40°C	5.68 A
Rated current at 45°C	5.52 A
Rated current at 50°C	5.35 A
Rated current 55°C	5.17 A
Rated current 60°C	4.99 A
Rated current 65°C	4.80 A
Rated current 70°C	4.60 A

**Architecture**

Type of pole	1P
Curve	D

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect

---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
Grid distance	60 mm

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	1.33 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	17.50 mm
Depth	70 mm