



WBQP2S-MW

FIN DGPO 10A MW

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|----------------|-------------------------------------|
| Colour | White |
| Surface finish | Matt |
| Material | Polycarbonate (PC) Thermoplastic |
| Treatment | Varnished |

Dimensions

| | |
|--------|--------|
| Height | 82 mm |
| Width | 120 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type | Screw mounting |

Equipment

| | |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert | No |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK08 |
| Ingress Protection (IP) class | IP20 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Texts

| | |
|--------------------|-----------------------------|
| Cover | Full cover plate |
| Protection | Enhanced contact protection |
| Type of connection | With screw terminals |

Suitable for

| | |
|---------|--|
| finesse | |
|---------|--|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |