



TRB201



Module 1 output 16A flush mounted KNX

Technical Features

Connectivity

| | |
|----------------|-----------|
| Radio protocol | KNX Radio |
|----------------|-----------|

Settings

| | |
|------------------------------|--------------------------|
| Supported configuration mode | ETS easy quicklink |
|------------------------------|--------------------------|

Connectivity

| | |
|---------------------------|-----|
| Receiver category | 2 |
| With bus system KNX | No |
| With bus system KNX radio | Yes |

Dimensions

| | |
|----------------|-------|
| Height | 30 mm |
| Built-in depth | 35 mm |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Materials

| | |
|--------|------------|
| Colour | Light grey |
|--------|------------|

Equipment

| | |
|-------------------------------|-----|
| Radio frequency bidirectional | Yes |
| With switch for manual switch | No |

Electric current

| | |
|-------------------|------|
| Switching current | 16 A |
|-------------------|------|

Frequency

| | |
|---------------------------|---------------------|
| Frequency | 50 - 60 Hz |
| Radio reception frequency | 868.30 - 868.30 MHz |

Power

| | |
|-------------------------------------|--------|
| Output power | 3680 W |
| 230 V incandescent and halogen lamp | 2300 W |

Voltage

| | |
|------------------------------|-------------|
| Operating voltage | 230 - 230 V |
| Rated operational voltage Ue | 230 - 230 V |
| System supply voltage | 230 V AC |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 0 - 45 °C |
|-----------------------|-----------|

Connection

| | |
|----------------------------------|---------------------|
| Cross-section rigid conductor | 2.5 mm ² |
| Cross-section flexible conductor | 2.5 mm ² |

Texts

| | |
|--------------------|--|
| Function | Easy additional functions: +6 scenes, repeater function Reset function (to factory setting) |
| Installation mode | For installation behind flush-mounted inserts |
| Type of connection | With screw-in lift terminals |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|