



TRB201



**Module 1 output 16A flush mounted KNX**

**Technical Features**

**Connectivity**

Radio protocol	KNX Radio
----------------	-----------

**Settings**

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

**Connectivity**

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

**Dimensions**

Height	30 mm
Built-in depth	35 mm

**Electric current**

Rated current	16 A
---------------	------

**Materials**

Colour	Light grey
--------	------------

**Equipment**

Radio frequency bidirectional	Yes
With switch for manual switch	No

**Electric current**

Switching current	16 A
-------------------	------

**Frequency**

Frequency	50 - 60 Hz
Radio reception frequency	868.30 - 868.30 MHz

**Power**

Output power	3680 W
230 V incandescent and halogen lamp	2300 W

**Voltage**

Operating voltage	230 - 230 V
Rated operational voltage Ue	230 - 230 V
System supply voltage	230 V AC

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	0 - 45 °C
-----------------------	-----------

**Connection**

Cross-section rigid conductor	2.5 mm <sup>2</sup>
Cross-section flexible conductor	2.5 mm <sup>2</sup>

**Texts**

Function	Easy additional functions: +6 scenes, repeater function Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

**Sustainability**

RoHS conform	Yes
--------------	-----