



EH711



Daily time switch 1 channel, analog, 72x72 with power reserve

Technical Features

Equipment

Number of channels

1

Frequency

Frequency

50 - 60 Hz

Power

Power consumption during operation

0.50 VA

230 V incandescent and halogen lamp

1000 W

Power incandescent lamp

1000 - 1000 W

Functions

Number of function channels

1

Connection

Number of contacts

1

Cross-section flexible conductor

1 - 6 mm²

Cross-section rigid conductor

1 - 4 mm²

Use conditions

Operating temperature

-10 - +45 °C

Dimensions

Height

72 mm

Width

72 mm

Depth

48.50 mm

Texts

Switch mode

Change-over contact

Installation mode

For surface mounting

Endurance

Electrical durability at nominal load in AC1 in operating cycles

50000

Texts

Type of connection

With screw terminals

Voltage

Rated operational voltage Ue

196 - 253 V

Power

Power loss at full load

1 W

Settings

Programme cycles

Programme cycle: 24 hours

Sustainability

RoHS conform

Yes