



HMX240

### MCB 2P 50kA C-40A 3M

#### Technical Features

##### Architecture

Type of pole	2P
Curve	C

##### Voltage

Rated operational voltage $U_e$	415 - 415 V
Type voltage supply	AC
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	6000 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Installation, mounting

Nominal tightening torque	3.5 - 5.0 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	Screw terminal

##### Electric current

Rated current	40 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 230 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 400 V AC IEC 60947-2	50 kA

##### Main electrical attributes

Rated short-circuit breaking capacity $I_{cn}$ AC according to IEC 60898-1	50 kA
--	-------

##### Installation, mounting

Nominal tightening torque down terminal	3.60 - 3.60 Nm
Nominal tightening torque top terminal	3.60 - 3.60 Nm

##### Power

Total power loss under $I_N$	7.28 W
------------------------------	--------

##### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

##### Connection

Cross-section of input and output with screws, for massive conductors	1 - 70 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 50 mm <sup>2</sup>
Cross-section flexible conductor	50 mm <sup>2</sup>
Cross-section rigid conductor	70 mm <sup>2</sup>

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Class of energy limitation $I^2t$	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

##### Capacity

Number of modules	3
-------------------	---

##### Connectivity

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

##### Dimensions

Height	90 mm
Width	53 mm
Depth	70 mm

**Sustainability**

REACH-SVHC free

Yes

**Illustrations | Drawings**

