

## Moulded Case Circuit Breaker X250 4P 25kA 100A TM

### Technical Features

#### Electric current

|                                                                                           |          |
|-------------------------------------------------------------------------------------------|----------|
| Rated current I <sub>N</sub>                                                              | 100 A    |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2 | 25 kA    |
| Rated current at 10°C according to IEC 60947                                              | 125 A    |
| Rated current at 15°C according to IEC 60947                                              | 122.20 A |
| Rated current at 20°C according to IEC 60947                                              | 119.30 A |
| Rated current at 25°C according to IEC 60947                                              | 116.20 A |
| Rated current at 30°C according to IEC 60947                                              | 113.20 A |
| Rated current at 35°C according to IEC 60947                                              | 110 A    |
| Rated current at 40°C according to IEC 60947                                              | 106.80 A |
| Rated current at 45°C according to IEC 60947                                              | 103.40 A |
| Rated current at 50°C according to IEC 60947                                              | 100 A    |
| Rated current at 55°C according to IEC 60947                                              | 96.40 A  |
| Rated current at 60°C according to IEC 60947                                              | 92.80 A  |
| Rated current at 65°C according to IEC 60947                                              | 89.10 A  |
| Rated current at 70°C according to IEC 60947                                              | 85.40 A  |

#### Architecture

|                           |                |
|---------------------------|----------------|
| Number of poles           | 4              |
| Control/operation element | Toggle         |
| Device construction type  | Fixed built-in |

#### Tripping

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

#### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

#### Voltage

|                                                  |             |
|--------------------------------------------------|-------------|
| Rated impulse withstand voltage U <sub>imp</sub> | 8000 V      |
| Rated insulation voltage U <sub>i</sub>          | 800 V       |
| Rated operational voltage U <sub>e</sub>         | 220 - 415 V |

#### Functions

|           |        |
|-----------|--------|
| Trip unit | TM F/F |
|-----------|--------|

#### Power

|                                     |         |
|-------------------------------------|---------|
| Power dissipation at I <sub>N</sub> | 17.70 W |
|-------------------------------------|---------|

#### Endurance

|                                        |      |
|----------------------------------------|------|
| Electric endurance in number of cycles | 1000 |
| Number of mechanical operations        | 4000 |

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

#### Connection

|                                  |                          |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 35 - 150 mm <sup>2</sup> |
| Cross-section rigid conductor    | 35 - 185 mm <sup>2</sup> |

#### Installation, mounting

|                               |            |
|-------------------------------|------------|
| Nominal tightening torque     | 12 - 12 Nm |
| Mounting-/Connection Position | Front      |

#### Settings

|                                                           |         |
|-----------------------------------------------------------|---------|
| Adjustment range short-term delayed short-circuit release | 0 - 0 A |
|-----------------------------------------------------------|---------|

#### Compatibility

|                       |    |
|-----------------------|----|
| Suitable for DIN Rail | No |
|-----------------------|----|

|                                   |          |
|-----------------------------------|----------|
| <b>Main electrical attributes</b> |          |
| Magnetic protection trip time     | 0 - 0 ms |
| <b>Sustainability</b>             |          |
| REACH-SVHC free                   | Yes      |
| RoHS conform                      | Yes      |