



MY120

### MCB 1P 4.5kA C-20A 1M

#### Technical Features

##### Electric current

|   |         |
|---|---------|
| Rated current   | 20 A    |
| Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1 | 4.50 kA |

##### Architecture

|              |    |
|--------------|----|
| Type of pole | 1P |
| Curve        | C  |

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Main electrical attributes

|   |         |
|---|---------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 4.50 kA |
|---|---------|

##### Installation, mounting

|   |                |
|---|----------------|
| Nominal tightening torque top terminal  | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

##### Voltage

|  |             |
|--|-------------|
| Rated operational voltage U <sub>e</sub>         | 230 - 400 V |
| Type voltage supply                              | AC          |
| Rated insulation voltage U <sub>i</sub>          | 500 V       |
| Rated impulse withstand voltage U <sub>imp</sub> | 4000 V      |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Connection

|  |                        |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors  | 1 - 35 mm <sup>2</sup> |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for flexible conductors            | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for massive conductors             | 1 - 35 mm <sup>2</sup> |
| Cross-section flexible conductor                                       | 1 - 25 mm <sup>2</sup> |
| Cross-section rigid conductor  | 1 - 35 mm <sup>2</sup> |

##### Installation, mounting

|   |                |
|---|----------------|
| Nominal tightening torque                     | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect      |
| Type of top connection for modular devices    | Screw terminal |
| 360° mounting position possible               | Yes            |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Use conditions

|  |                  |
|--|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2                |
| Class of energy limitation I <sup>2</sup> t              | 3                |
| Air humidity protection                                  | For all climates |
| Operating temperature                                    | -25 - 70 °C      |

##### Power

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 2.70 W |
|---------------------------------------|--------|

##### Connectivity

|   |                  |
|---|------------------|
| Type of connection                            | Screw terminal   |
| Top connection alignment for modular devices  | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

|                       |  |          |
|-----------------------|--|----------|
| <b>Dimensions</b>     |  |          |
| Height                |  | 83 mm    |
| Width                 |  | 17.50 mm |
| Depth                 |  | 70 mm    |
| <b>Sustainability</b> |  |          |
| RoHS conform          |  | Yes      |