



EH711



IP20



Daily time switch 1 channel, analog, 72x72 with power reserve

Technical Features

Equipment

Number of channels 1

Frequency

Frequency 50 - 60 Hz

Power

Power consumption during operation 0.50 VA

230 V incandescent and halogen lamp 1000 W

Power incandescent lamp 1000 - 1000 W

Functions

Number of function channels 1

Connection

Number of contacts 1

Cross-section flexible conductor 1 - 6 mm²

Cross-section rigid conductor 1 - 4 mm²

Use conditions

Operating temperature -10 - +45 °C

Dimensions

Height 72 mm

Width 72 mm

Depth 48.50 mm

Texts

Switch mode Change-over contact

Installation mode For surface mounting

Endurance

Electrical durability at nominal load in AC1 in operating cycles 50000

Texts

Type of connection With screw terminals

Voltage

Rated operational voltage Ue 196 - 253 V

Power

Power loss at full load 1 W

Settings

Programme cycles Programme cycle: 24 hours

Sustainability

RoHS conform Yes