



CDA240SC

**RCCB auto reclosing 1P+N 40A 30mA A 3M**

**Technical Features**

**Architecture**

Type of pole	1P+N
--------------	------

**Electric current**

Rated current	40 A
Rated residual operating current I <sub>dn</sub>	30 mA
Breaking and opening capacity I <sub>dm</sub>	0.63 kA
Rated conditional short-circuit current I <sub>nc</sub> according to EN61008-1	6 kA
Rated current -25°C	40 A
Rated current at -20°C	40 A
Rated current -15°C	40 A
Rated current -10°C	40 A
Rated current -5°C	40 A
Rated current at 0°C	40 A
Rated current 5°C	40 A
Rated current 10°C	40 A
Rated current 15°C	40 A
Rated current at 20°C	40 A
Rated current 25°C	40 A
Rated current 30°C	40 A
Rated current 35°C	40 A
Rated current at 40°C	40 A

**Installation, mounting**

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	230 - 230 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	253 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Capacity**

Number of modules	3
-------------------	---

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Installation, mounting**

Nominal tightening torque	2 - 2 Nm
---------------------------	----------

**Connection**

Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1.5 - 35.0 mm <sup>2</sup>

**Power**

Total power loss under I <sub>N</sub>	5.40 W
---------------------------------------	--------

**Use conditions**

Air humidity protection	95%/55°C
Max. Altitude	2000 m

---

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Dimensions**

Height	106 mm
Width	54 mm
Depth	75 mm