



SVN122

Red LED Indicator light 230VAC

Technical Features

Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Voltage

|                                      |             |
|--------------------------------------|-------------|
| Rated insulation voltage Ui          | 250 V       |
| Rated impulse withstand voltage Uimp | 4000 V      |
| Rated operational voltage Ue         | 230 - 230 V |
| Type voltage supply                  | AC          |

Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -20 - 50 °C |
| Storage/transport temperature | -40 - 80 °C |

Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Connection

|                                  |               |
|----------------------------------|---------------|
| Cross-section flexible conductor | 0.75 - 6 mm²  |
| Cross-section rigid conductor    | 0.75 - 10 mm² |

Power

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 0.80 W |
|---------------------------|--------|

Dimensions

|        |          |
|--------|----------|
| Height | 83 mm    |
| Width  | 17.50 mm |
| Depth  | 62 mm    |

Lighting

|              |     |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Connection

|                     |     |
|---------------------|-----|
| Type of lamp socket | Fix |
|---------------------|-----|

Materials

|        |     |
|--------|-----|
| Colour | Red |
|--------|-----|

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Power

|                          |      |
|--------------------------|------|
| Power per charging point | 0 kW |
|--------------------------|------|