



HDA098Z

**Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 100A 18kA CTC**

**Technical Features**

**Electric current**

Rated current	100 A
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	122,20 A
Rated current 15°C according to IEC 60947	119,70 A
Rated current 20°C according to IEC 60947	117 A
Rated current 25°C according to IEC 60947	114,40 A
Rated current 30°C according to IEC 60947	111,60 A
Rated current at 35°C according to IEC 60947	108,80 A
Rated current at 40°C according to IEC 60947	106 A
Rated current 45°C according to IEC 60947	103 A
Rated current 50°C according to IEC 60947	100 A
Rated current 55°C according to IEC 60947	96,80 A
Rated current at 60°C according to IEC 60947	93,60 A
Rated current 65°C according to IEC 60947	90,20 A
Rated current 70°C according to IEC 60947	86,70 A

**Architecture**

Number of poles	1
Neutral position	Without neutral

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Power**

Total power loss under IN	8,40 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Settings**

Thermal protection knob setting xIN	1
	1

**Dimensions**

Height	130 mm
Width	25 mm
Depth	68 mm

**Compatibility**

Suitable for DIN Rail

No

**Main electrical attributes**

Magnetic protection trip time

0 - 0 ms

**Sustainability**

REACH-SVHC free

Yes

RoHS conform

Yes