

# Product Datasheet

## NCN406



NCN406

### MCB 4P 10kA/15kA C-6A 4M

#### Technical Features

##### Electric current

Rated current	6 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	15 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	30 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	15 kA
Rated current -25°C	7.61 A
Rated current at -20°C	7.48 A
Rated current -15°C	7.35 A
Rated current -10°C	7.21 A
Rated current -5°C	7.07 A
Rated current at 0°C	6.93 A
Rated current 5°C	6.78 A
Rated current 10°C	6.63 A
Rated current 15°C	6.48 A
Rated current at 20°C	6.32 A
Rated current 25°C	6.16 A
Rated current 30°C	6 A
Rated current 35°C	5.81 A
Rated current at 40°C	5.61 A
Rated current at 45°C	5.41 A
Rated current at 50°C	5.19 A
Rated current 55°C	4.97 A
Rated current 60°C	4.74 A
Rated current 65°C	4.50 A
Rated current 70°C	4.24 A

##### Architecture

Type of pole	4P
Curve	C

##### Capacity

Number of modules	4
-------------------	---

##### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

##### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

##### Voltage

Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

##### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect

### Installation, mounting

Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C

### Power

Total power loss under IN	5.44 W
---------------------------	--------

### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

### Dimensions

Height	83 mm
Width	70 mm
Depth	70 mm

### Illustrations | Drawings

