



NCN104

**MCB 1P 10kA C-4A 1M**

**Technical Features**

**Electric current**

Rated current	4 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	7.50 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	15 kA
Rated current -15°C	4.99 A
Rated current -10°C	4.89 A
Rated current -5°C	4.79 A
Rated current at 0°C	4.68 A
Rated current 5°C	4.58 A
Rated current 10°C	4.47 A
Rated current 15°C	4.35 A
Rated current at 20°C	4.24 A
Rated current 25°C	4.12 A
Rated current 30°C	4 A
Rated current 35°C	3.87 A
Rated current at 40°C	3.74 A
Rated current at 45°C	3.61 A
Rated current at 50°C	3.47 A
Rated current 55°C	3.33 A
Rated current 60°C	3.17 A
Rated current 65°C	3.01 A
Rated current 70°C	2.85 A

**Architecture**

Type of pole	1P
Curve	C

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm
Nominal tightening torque	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	240 - 415 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

**Safety**

Ingress Protection (IP) class	IP20
Grid distance	60 mm

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	2.62 W
---------------------------	--------

**Connectivity**

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	17.50 mm
Depth	70 mm

**Illustrations | Drawings**

