



MT216A

## MCB 2P 6kA B-16A 2M

### Technical Features

#### Electric current

Rated current	16 A
Rated current -15°C	19.30 A
Rated current -10°C	19 A
Rated current -5°C	18.60 A
Rated current at 0°C	18.30 A
Rated current 5°C	17.90 A
Rated current 10°C	17.60 A
Rated current 15°C	17.20 A
Rated current at 20°C	16.80 A
Rated current 25°C	16.40 A
Rated current 30°C	16 A
Rated current 35°C	15.60 A
Rated current at 40°C	15.20 A
Rated current at 45°C	14.70 A
Rated current at 50°C	14.30 A
Rated current 55°C	13.80 A
Rated current 60°C	13.30 A
Rated current 65°C	12.90 A
Rated current 70°C	12.40 A

#### Architecture

Type of pole	2P
Curve	B

#### Capacity

Number of modules	2
-------------------	---

#### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

#### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

#### Voltage

Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

#### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

# Product Datasheet

## MT216A

---

### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

### Power

Total power loss under IN	5.10 W
---------------------------	--------

### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

### Dimensions

Height	83 mm
Width	35 mm
Depth	70 mm

### Sustainability

RoHS conform	Yes
--------------	-----